

## Sikla Extension Modul1 imperial

Minimale Größe	bis	Maximale Größe	Langbezeichnung
----------------	-----	----------------	-----------------

Rohrklasse: SuCri Module 1 - Sikla Extension - Imperial

Description:

Speicherort der Datei: D:\Documents\2025\_CPAKS\Spec Sheets\SuCri Module 1 - Sikla Extension - Imperial.psp

Zuletzt gespeichert: 30.08.2024 17:46:30

----- Pipe -----			
1/2"	to	80"	Pipe
----- Support -----			
1/2"	to	4"	BG11 MS41-1/2"
1/2"	to	4"	BG11 MS41-M10
1/2"	to	4"	BG13 MS41-1/2"
1/2"	to	4"	BG13 MS41-M10
1/2"	to	4"	BG14 F80-1/2"
1/2"	to	4"	BG14 F80-M10
1/2"	to	4"	BG15 F80-1/2"
1/2"	to	4"	BG15 F80-M10
1/2"	to	4"	BG16 F100-1/2"
1/2"	to	4"	BG17 F100-1/2"
1/2"	to	12"	BG22 F100
1/2"	to	6"	BG22 F80
1/2"	to	4"	BG42 MS41-1/2"
1/2"	to	4"	BG44 F80-1/2"
1/2"	to	4"	BG45 F80-1/2"
1/2"	to	4"	BG48 MS41-1/2"
1/2"	to	4"	BG49 F100-1/2"
1/2"	to	4"	BG50 F100-1/2"
1/2"	to	6"	BG51 F80
1/2"	to	12"	BG52 F80/100
1/2"	to	4"	BG54 F100
1/2"	to	4"	BG57 MS41
1/2"	to	4"	BG60 T100-1/2"
1/2"	to	4"	BG61 T100-1/2"
1/2"	to	12"	FR-H 20
1/2"	to	6"	LA-HV 150
1/2"	to	6"	LA-HV 200
1/2"	to	6"	LA-HV 90
1/2"	to	12"	LC-HV 150
1/2"	to	12"	LC-HV 200
1/2"	to	12"	LC-HV 90
8"	to	24"	LD-HV 150
8"	to	24"	LD-HV 200
8"	to	24"	LD-HV 90
1"	to	12"	LK-HV 150
1/2"	to	12"	LR-H 20

1"	to	21in	STABIL D-A
8"	to	21in	STABIL D-M16
1/2"	to	21in	STABIL D-M16 mE
12"	to	16"	STABIL D-M16 SILICON
1/2"	to	10"	STABIL D3G
1/2"	to	10"	STABIL D3G mE
1/2"	to	10"	STABIL D3G SILICON
1/2"	to	24"	STABIL RB-A
4"	to	4"	TP F 100/100
4"	to	4"	TP F 100/160
3"	to	3"	TP F 80/30
3"	to	3"	TP F 80/80
1/2"	to	12"	XR-H 20